LINHOF CINE ROLLEX ALL-PERF MOD

This back can be easily modified for all-perf use. The modification is non-reversible, but once it has been completed, the back will be able to shoot all forms of 70mm film (perforated and unperforated), as well as 65mm film.

1. Using either a Dremel rotary tool and a cut-off blade, a file, or a very sharp knife, cut or grind away all of the teeth on the three sprocket wheels in the back's insert:





2. Use ¼ inch dental elastics (for braces), inserting eight (8) in the locations shown below:



That's it! Your back will now accept all forms of 70mm and 65mm film!

